


■ Vers. 727+728




■ Vers. 727+728



SCHEMATICS



COMPOSITION EXAMPLES



TECHNICAL INFORMATION

*	COVERING	Leather ✓	Soft Cover ✓			
*	OPTIONS	Removable	Contrast Stitching			
4	FILLING	Arms [Fiber Seat Foam Feather/Fiber Mix Feather	cushion Fiber Foam Feather/Fiber M Feather	Back cushion	Fiber Foam Feather/Fiber Mix Feather
<u>L</u>	COMFORT	Standard Comfor	t Firm Comfort			
*	FUNCTION	Bed	Electric motion	Motion	Recliner	Sliding
	VISUAL APPEARANCE*	Low ✓	Medium	High		
#	LEGS	Wood	Metal ✓	Plastic	Castors	Upholstered
VISUAL APPEARANCE						
The product may reveal various wrinkles due to the combination of Elasticity of the covering, characteristics of the interior construction and the design of the product.						
	Low	<u>// N</u>	ledium	High		
Products with Visual Appearance listed as High or Medium would require higher degree of care, where seats and back cushions may require fluffing and plumping more often than Products with Visual Appearance listed as Low						

NOTES

- Designed by Natuzzi Design Center.
- Date of launch: 2024.
- With its unique design, Snail captures the elegance and functionality of nature.
 Its side shape is reminiscent of the elegant silhouette of a snail, while the translating backrest emulates the fluid and reassuring movement of a snail retracting into its shell.
- Available in leather or fabric.
- In leather the model is available starting from cat. 15 (Le Mans).
- Model is not available with article Misterbianco (cat. 30).
- The piping running around the entire perimeter of the sofa can be tone-on-tone in the same leather or in contrast when in fabric. If the main covering chosen is fabric the contrast piping can be done in leather CAT 15 Le Mans, CAT 25 Status, CAT 30 Stromboli e CAT 40 Siena.
- A sliding mechanism on all modules allows the backrest to be shifted by approx 400 mm, so as to have customized comfort modifying the seat depth from approx 60cm to 100cm.
 This allows the seat to be used as a casual seat or as a compact chaise longue.
- Available with Soft Touch mechanism that customize the back cushion depth with a tap.
 The buttons are positioned on the internal side of the arm for versions 727/728 and on the internal right side of the seat for versions 761/790.

NOTES

- A battery pack can be ordered with its own version 830. For order entry please use XX for category and XXX for cover code.
- The battery pack has to be connected to the back of the chair by removing the power supply cable. It is strongly recommended to order one battery bank per motion seat in order to guarantee a long life.
- Upholstered side
- Removable hooks on each seating module.
- The hidden metal feet with anti-scratch and non-slip rubbers offer a practical solution for protecting floors.